



THE HANSON GROUP. LLC
GOOD PEOPLE, GREAT SCIENCE

3044 Adriatic Court, Peachtree Corners, GA 30071

(P) 770-495-9554 (F) 404-521-4396

sales@thehansongroup.com

www.thehansongroup.com

UV-770

TECHNICAL DATA SHEET

Product Name:	Bis(2,2,6,6-tetramethyl-4-piperidine)sebacate
Synonyms:	UV-770
CAS No.	52829-07-9
Empirical Formula	C ₂₂ H ₂₉ N ₃ O
Formula Weight	481

Test

Appearance:	White with light yellow powder or pellet
Assay (G.C.):	99.0% min.
M.P., °C:	81.0 ~ 85.0 °C
Light Transmittance	
425 (nm)	98.0% min.
500 (nm)	99.0% min.

Specification

Characterization:

UV- 770 is a hindered amine light stabilizer (HALS) for applications demanding particularly high light stability. It provides excellent light stability for thick sections but can also be used for articles with a high surface area such as films and tapes.

Application:

UV- 770 is recommended to be used in polypropylene, impact modified PP (TPO), EPDM, polystyrene, impact polystyrene, ABS, SAN, ASA and polyurethanes and is also effective in polyamides and polyacetals.

Features:

UV-770 is a low molecular weight hindered amine light stabilizer that provides excellent light stability for thick sections and films in the recommended substrates. The benefit of using UV-770 is the high, light-stabilizing performance, particularly in PP thick sections. It has broad compatibility and can be easily dispersed. Compared to conventional UV-absorbers, the effectiveness of UV-770 is less dependent on the polymer's thickness. For this reason, the use of UV-770 also provides good light stability in articles with higher specific surface, e.g. films and tapes.



THE HANSON GROUP. LLC
GOOD PEOPLE, GREAT SCIENCE

3044 Adriatic Court, Peachtree Corners, GA 30071

(P) 770-495-9554 (F) 404-521-4396

sales@thehansongroup.com

www.thehansongroup.com

- Storage:** Keep container tightly closed, in a cool place and away from moisture and heat. Protect from fire, static discharges, acids and acid forming substances.
- Package:** UV-770 is available in 25 kg carton box with inner anti-static PE bag.
- Safety:** Handle with care and avoid unnecessary personal contact. Avoid continuous or repetitive breathing of dust. Use only with adequate ventilation. Avoid contact with eyes. Avoid release to the environment. Avoid dust formation and ignition sources.
- Shelf life:** 24 months under recommended storage conditions. After 24 months, retest material.
-